

PL₁


FIRST-ORDER PRECISION LEVEL

42X Telescope Magnification 0.2mm Standard Deviation for 1km Double-run Levelling





The foremost instrument in its field; free free



HIGH PERFORMANCE GIVING THE HIGHEST POSSIBLE


Sokkia's PL1 is the product of extensive experience in the field of high technology and sophisticated instrument making. The PL1 First Order Precision Level was developed after long and thorough research into every aspect of use under all possible working conditions. The PL1 has been subject to strict quality control to ensure high accuracy and ease of use. The combination of a tilting mechanism with a sensitivity of 10"/2mm, a coincidence type observation mechanism, and an optical micrometer with a direct reading of 0.1mm, combine to guarantee precise levelling and accurate measurement.


TILTING SCREW MECHANISM FOR FINE ADJUSTMENT OF

The tilting screw used to level the line of sight is engraved with graduations that accurately indicate the inclination, and index lines that indicate the number of turns of the tilting screw. The tilting screw is divided into 50 equal divisions, each division equalling 2" of inclination.


COINCIDENCE TYPE OPTICS GIVE SHARP BUBBLE IMAGE.

Innovative optical design has been used in the coincidence bubble reading optics to ensure a sharp image of the bubble which is magnified to twice normal size. The C or mark that appears on the bubble image quickly indicates the direction in which the tilting screw is to be turned to achieve coincidence.





om error even under the most difficult surveying conditions, yet convenient and leasy to use.



ACCURACY — FIRST-ORDER PRECISION LEVEL PL1

OPTICAL MICROMETER ALLOWS PRECISE READING


The PL1 is equipped with an optical micrometer which enables staff graduations to be subdivided directly to 0.1mm, and to 0.01mm by estimation. The micrometer knob is turned until the graduation line on the staff bisects the wedge-shaped reticle lines of the PL1 telescope. The shift is numerically displayed in the optical micrometer window, and this reading is added to the staff reading to give direct reading accuracy to 0.01mm.


WEDGE SHAPED RETICLE FOR PRECISE READING


The high resolution telescope, which gives a sharp image of the target, is provided with a wedge-type reticle to read staff graduations more accurately. The distance to the staff can be easily obtained using the stadia lines.

OPTICAL WEDGE PROVIDES EASY AND FINE ADJUSTMENT OF LINE OF SIGHT.

The adjustment to the line of sight is simple. It is not necessary to adjust screws on the tubular level. Simply turn the optical wedge until the line of sight is horizontal to get exact results.







SPECIAL TRIPOD FOR PL1, PLW1


PLW1 is a wooden, non-telescopic precision tripod exclusively designed for the first-order precision level, PL1. Made of seasoned wood carefully selected and dried over a long period, and designed for effective absorption of vibrations, this tripod is virtually unaffected by sunlight or the passage of time. The red marking, which is helpful for setting up in the desired direction at any survey point, the wear-resistant leg tips made of a special alloy, and many other design considerations make this tripod durable and easy to use.



GS1 NEW SUPER INVAR STAFF

Designed exclusively for first-order surveying. Graduations are calibrated using laser interferometer technology and inscribed on New Super Invar tape. The tape and the frame offset expansion yielding coefficients of thermal expansion of zero.

Effective length ······3m
Scale divisions ······10mm
Size3069(L) × 100(W) × 51(H)mm
Weight (1 pc.)5.6kg
A complete set includes two staves in a
wooden case.



SPECIFICATIONS

Total
Telescope Length303mm
Objective aperture50mm
Image ····· Erect
Magnification42×
Resolving power2"
Field of view (at 100m) ······1°10 (2.0m)
Minimum focus······2.0m
Stadia multiplication constant ······100
Main Level
Sensitivity ······10"/2mm
Observation ····· Bubble Coincidence
Magnification·····×2
Levelling Accuracy
Standard deviation for 1km
double run levelling0.2mm (0.008in.)
Circular Level
Sensitivity ·······3.5 /2mm
Micrometer
Measuring Range·····10mm
Scale division0.1mm
Tilting Mechanism
Tilting Range·····±5.8
One Revolution of Knob ······100"
Size
Dimensions ·· 303(L)×140(W)×180(H)mm
Weight
Main Unit ······4.8kg

STANDARD SET

PL1 main unit ······1
Lens cap1
Vinyl cover ·····1
Tool kit1
Operator's manual ·····1
Carrying case ·····1

SOKKIA CO., LTD.

ISO9001 Certified (JOA-0557) http://www.sokkia.co.jp/english/ INTERNATIONAL SALES DEPARTMENT 260-63 HASE, ATSUGI, KANAGAWA, 243-0036 JAPAN PHONE +81-46-248-7984 FAX +81-46-247-1731

